


0606 KSS Nylon Cable Gland (PG Thread)



- Material: UL approved Nylon 66, 94V-2
 - Color: Black, available in other colors.
 - Suit a variety of applications, and diverse industries.
 - Function :Mount gland to pre-drilled panel hole, use locknut to fix gland on board, insert the cables in the seal,and then tighten up the nut to hold cables in position.
 - Feature : Simply and quickly fixed, high degree of the protection IP68 preventing dust and water.
 - Available to order the accessories separately. Follow the drawing and add the letter to the suffix part number,L for locknut, W for washer, B for gland body, S for seal, N for nut. For example, EGL-7 if you would like to only order locknut for PG7.
- ※ EG-7LS has smaller nut.
- ※ Protection : IP68 (only if the washer is assembled)



											Unit: mm
	Item No.	Thread	Mounting Hole	D1	D2	B1	L1	L2	L3	Cable Range	Packing
<input type="checkbox"/>	EG-7	PG-7	12.5~12.8	12.5	8.3	6.9	7.9	20.0	13.3	3.5 ~ 6	50 pcs / Bag
<input type="checkbox"/>	EG-7LS	PG-7	12.5~12.8	12.5	8.3	6.9	7.9	20.0	13.3	3.5 ~ 6	
<input type="checkbox"/>	EG-9	PG-9	15.2~15.5	15.2	10.5	8.0	8.2	22.0	15.1	4 ~ 8	
<input type="checkbox"/>	EG-9L	PG-9	15.2~15.5	15.2	10.5	8.0	14.7	22.0	15.1	4 ~ 8	
<input type="checkbox"/>	EG-11	PG-11	18.3~18.9	18.3	13.2	10.5	7.9	23.7	18.3	5 ~ 10	
<input type="checkbox"/>	EG-11L	PG-11	18.3~18.9	18.3	13.2	10.5	14.9	23.7	18.3	5 ~ 10	
<input type="checkbox"/>	EG-13.5	PG-13.5	20.4~20.7	20.4	15.5	12.0	8.9	24.6	18.9	6 ~ 12	
<input type="checkbox"/>	EG-13.5L	PG-13.5	20.4~20.7	20.4	15.5	12.0	15.8	24.6	18.9	6 ~ 12	
<input type="checkbox"/>	EG-16	PG-16	22.5~22.8	22.5	17.2	14.0	9.8	26.2	19.5	10 ~ 14	
<input type="checkbox"/>	EG-21	PG-21	28.3~28.7	28.3	22.4	18.4	10.8	30.0	23.7	13 ~ 18	
<input type="checkbox"/>	EG-29	PG-29	37.0~37.4	37.0	30.6	25.0	10.8	35.0	27.4	18 ~ 25	25 pcs / Bag
<input type="checkbox"/>	EG-36	PG-36	47.0~47.4	47.0	35.3	35.5	14.5	42.3	30.3	22 ~ 32	10 pcs / Bag
<input type="checkbox"/>	EG-42	PG-42	54.0~54.4	54.0	47.0	40.0	14.5	44.0	31.2	30 ~ 38	
<input type="checkbox"/>	EG-48	PG-48	59.3~59.7	59.3	43.2	46.0	16.7	42.7	31.3	34 ~ 44	

[Input Sample Order](#)

[Check Selected](#)

[Return All Selected](#)